

General Specifications

Model PH21
Wide Body Sensor for Water and Waste Water

GS 12B06J10-01EN-P

■ Overview

The PH21 sensor is targeted for water and waste water industry where simplicity will result in accuracy and reliable pH measurement. This means that in 80% of the water- and waste water industry, this sensor will be an excellent choice.

For more difficult applications than water, we refer you to other sensors in our pH portfolio.

The PH21 is the newest wide body sensor in Yokogawa. This sensor is specially made for water- and waste water industry.

■ Features

- The sensor body is made from recycled product.
- Preferred to work with SA11 SENCOM SMART
- Adapter model SA11.
- Our highly accurate instruments help you increase product efficiency, improve product quality and ensure process safety.
- Increase product efficiency due to the memory chip in the sensor.



1. General Specifications

Measuring elements	: pH glass electrode
	: Silver Chloride reference
	: Pt1000 temp sensor

Construction materials

Wetted parts

Sensor body	: PPS- GF40
Measuring sensor	: G-Glass
O-ring	: Viton
Reference junction	: PTFE

Functional specifications (at 25°C)

Isothermal point	: pH7
Reference system	: Ag/AgCl
Glass impedance	: 100-300 MΩ
Junction resistance	: < 1 KΩ
Temperature element	: Pt1000 IEC 751
Asymmetry potential	: 8 mV ± 15 mV
Linearity PH (Slope)	: >96% in pH 2-12

Dynamic specifications (at 25°C)

Response time pH step 7 to 4	: 15 sec for 90%
Response time temp step 10°C	: 120 sec for 90%
Stabilization time (0.02 pH unit/10 s)	: < 2 minutes

Operating range

pH	: 0-14
Temperature	: +0°C ... +60°C
Pressure (at 25°C)	: 0 to 5 Bar (0 to 72 PSIG)
Pressure (at 70°C)	: 0 to 5 Bar (0 to 72 PSIG)
Conductivity	: > 50 μS/cm




Figure 1: Pressure & Temperature range PH21

Note: The pH operating range at room temperature is 0-14 pH, but at high temperatures, the lifetime will be seriously shortened outside 3-11 pH range.

Note: For detailed information about SENCOM SMART Adapter SA11 refer to current edition of GS12A06S01-01Z1x.

Selection options

PH21	
Cable	: WE10
Smart adapter extension cable	: WE10-003-V1
Flow fitting	: FF40+ option /FPS or K1523DD
Immersion	: FD40+option /FPS or K1523DD
Subassembly	: FS40+option /FPS or K1523DD
Option HCNF	: K1547PJ

2. Dimensions




Figure 2a: Dimensions spare part K1547PJ (Hastelloy cleaning system) and adapters




Figure 2b: Dimensions spare parts K1523DD (PH20-mounting in F*40), K1547PK (Adapter 1" NPT, SS 316 for PH21), K1547PL (Adapter 1" BSP, SS 316 for PH21)

Dimensions PH21




Figure 3 : Connection diagram




Figure 4: Dimensions PH21

■ 3. Model Codes & Parts

Table 1: Model and suffix codes for PH21

Model	Suffix Code	Description
PH21		Wide Body sensor specially for water and wastewater applications
Connection	-VS	VarioPin with ID-chip for Sencom 4.0 connector (model SA11)
Type	-RTD	PPS body / Tapered Thread / Dome shaped
Style	-NN	Always -NN

Table 2: Spare parts PH21

Spare part		Description
K1523DD	PH21	/FPS Adapter for FF40, FS40 and FD40 fittings (PPO)
K1547PK		/NSS 1" NPT, Stainless Steel adapter (Viton O-ring)
K1547PL		/BSS ISO 7/1-R1, Stainless Steel adapter (Viton O-ring)
K1547PM		/NTI 1" NPT, Titanium adapter (Viton O-ring)
K1547PN		/BTI ISO 7/1-R1, Titanium adapter (Viton O-ring)
K1521JD		Holder for FU20 in FF20-S3* (SS)
K1521JE		Holder for FU20 in FF20-S3* (PVDF)
K1521JF		Holder for FU20 in FF20-S3* (PP)
K1500FR		Viton O-rings 29.82*2.62 (5 pcs) for 1" adapter
K1500FS		EPDM O-rings 29.82*2.62 (5 pcs) for 1" adapter
K1500FT		Silicone O-rings 29.82*2.62 (5 pcs) for 1" adapter
K1526RF		Protection CAP/WET-POCKET FU20 (10 PCS)
K1547PJ	Cleaning system for FU20	Hastelloy cleaning system (HCNF)
K1547PG		Hastelloy nozzle and mounting set (HCNF)
K1547PH		Nylon tube (10 metre) and tube mounting set for chemical cleaning system
K1521TA	Buffer Capsules (1 bottle= e80 capsules)	Buffer Capsules for pH 1.68 @25°C
K1521TB		Buffer Capsules for pH 4.01 @ 25°C
K1521TC		Buffer Capsules for pH 6.87 @ 25°C
K1521TD		Buffer Capsules for pH 10.01 @ 25°C
K1521TE		Buffer Capsules for pH 12.45 @ 25°C
K1521TF		Buffer Capsules Combo package for pH 4.01/6.87/10.01@ 25°C
K1522PS	Part K1522PS Protection sleeve	Protection sleeve for 3/4" NPT sensor

Connection equipment

BA11	Active junction connection box
WE10	Multicore shielded cable with two low noise coaxes and four insulated wires, halogen free.
SA11	SENCOM SMART adapter

Cleaning system for PH21

Some applications require frequent cleaning of the electrode. For these applications Yokogawa designed a chemical cleaning system that can either be used in the Yokogawa fitting range (HCN2, HCN3 or HCN4) or as back-end spare part for the PH21. The K1547PJ spare part (previously ordered as /HCNF) option comes with a hastelloy cleaning nozzle, stainless steel mounting and ferrules sets and a nylon tube of 10 meters

Spare part K1547PJ (previous /HCNF option)




Figure 5: Installation example using spare part K1547PJ

YOKOGAWA ELECTRIC CORPORATION
World Headquarters
9-32, Nakacho 2-chome, Musashino-shi
Tokyo 180-8750
Japan
www.yokogawa.com

YOKOGAWA CORPORATION OF AMERICA
2 Dart Road
Newnan GA 30265
USA
www.yokogawa.com/us

YOKOGAWA EUROPE BV
Euroweg 2
3825 HD AMERSFOORT
The Netherlands
www.yokogawa.com/eu

YOKOGAWA ELECTRIC ASIA Pte. LTD.
5 Bedok South Road
Singapore 469270
Singapore
www.yokogawa.com/sg

YOKOGAWA CHINA CO. LTD.
Room 1801, Tower B, THE PLACE
No.100 Zunyi Road
Changning District, Shanghai, China
www.yokogawa.com/cn

YOKOGAWA MIDDLE EAST B.S.C.(c)
P.O. Box 10070, Manama
Building 577, Road 2516, Busaiteen 225
Muharraq, Bahrain
www.yokogawa.com/bh

Yokogawa has an extensive sales and distribution network.

Please refer to the European website (www.yokogawa.com/eu) to contact your nearest representative.

YOKOGAWA ◆

Printed in The Netherlands, 02-2506